





Benefit from Zeppelin's global leadership in mixing technology!

Based on the pioneering HENSCHEL-Mixers® Zeppelin has been setting standards in the mixing technology for decades and has well-proven expertise in the areas of plastics, additives, colors, paints, pigments, toners, food, ceramics, minerals and metal compounds.

We know what is important and we have the skills to process and handle sensitive materials. We offer ground-breaking solutions for any mixing task and procedure as well as for up- and down-stream handling and processing.

The mixing technology of the 21st century is characterized by innovations, inventiveness and solution-oriented engineering. As one of the world leading mixing technology experts we not only provide mixers and mixing solutions but understand the entire manufacturing process.

Perfect first-hand mixing solutions


Container Mixers are versatile mixers providing enormous benefits for many applications (e.g.: color toner, TPU/TPE, technical polymers like Peek and PTFE, any additive premix, masterbatches, powder coatings) thus achieving excellent qualities in homogenizing, dispersing and coloring for bulk materials.

Unlike for stationary installed mixers, the mixing bowl (container) is movable. Filling and discharging can be done remotely from the mixing station.

The new Container Mixer CMQ

Specially designed for coloring applications, mainly Powder Coatings and Color Masterbatch, the CMQ provides highest flexibility and reduces cleaning time to a minimum. Integrated in an automated material handling system, Zeppelin offers a sophisticated process solution. This innovation ensures our customers a competitive edge in the international market.





L black

Q-Panels

Colormark test specimens

CIELAB Color Space

The three coordinates represent the lightness (L* = 0 yields black and L* = 100 white), the position between red and green (a* \leq 0 green, a* \geq 0 red) and the position between yellow and blue (b* \leq 0 blue and b* \geq 0 yellow) of the color.

Optimized design for best results

The innovative wing profile tool with its unprecedented lifting abilities makes the bottom shell radius and a deflection via that radius unnecessary. The tool is no longer near-ground and the special airfoil shape generates a suction effect that directs the material upwards. The combination of the flat mixing head with the wing profile tool provides high lifting forces, minimal turbulence and low mixing resistance. This ensures a fast and effective homogenization and a very good color strength.

Thanks to the high bottom clearance, no pressure is generated on the surface of the mixing head and any material deposits or build-ups are eliminated. This results in hardly any temperature increase (approx. 1.5 - 2 °C/min), a low power consumption and less wear on the mixing tool.

Watch and experience how efficient our mixers work



Scan or click





FIRST CLASS MIXING – MOST EFFICIENT CLEANING DESIGN Save up to 80 % cleaning time



Patented wing profile tool*

- Airfoil shaped mixing arms with winglets for lowest mixing resistance
- Optimized mixing with lowest cleaning effort





Fast and easy cleaning

- Flat panel mixing head
- Most minimal cleaning effort
- Unprecedented cleanability
- Allows shortest cleaning times



Safe handling

Monitored automatic container grounding




Monitoring of the bearings via vibration and gyroscopic sensors

ATEX

EU type-examination certificate for ATEX equipment category 1/3 D



- Container venting integrated in container seal
- Drop in two stages



No guiding installations

- Self centering container
- No obstacles on the floor for cleaning






(Mixer in mixing position)

DESIGNED FOR MAXIMUM EFFICIENCY







TECHNICAL DATA

Size	Net volume	Batch weight *
	[l]	[kg]
150	120	35-70
300	240	65-135
450	360	100-200
600	480	135-270
1000	800	225-450
1200	960	270-540
2000	1600	450-900
* Assuming an average bulk density $\rho_b = 0.6$ kg/l		


- Mixing time approx.3-5 minutes
- Mixing tool speed up to 15 m/s



CONTAINER SYSTEM AND SURROUNDINGS


Easy transport

- Rail conveyor
- Chain conveyor
- Roller conveyor
- AGV (Automated Guided Vehicle)
- Manual or with mover









Different container discharging solutions

- Drive-in
- Load-on



Container feeding

Automated or ·····: manual design for a precise loading solution

Operator Safety

Safety fence

or light barrier





Central aspiration unit

Efficient venting



Use different container sizes

■ Up to 3 different container volumes for the same machine size



WE MAKE YOUR BUSINESS EFFICIENT AND MANAGEABLE

Advantages at a glance

- Most efficient cleaning effort
 Reduces cleaning times up to 80 %
- Consistent color strength

 Low measurable Δ E

 (total color difference)



- Fast and effective
 homogenization
 Even distribution of all components
- High dispersion
 Prevention of any pigment
 agglomeration
 Equalizing of particle size
- Wide range of batch sizes
 Use different container sizes on one machine size

- Low mixing resistance
 Minimal temperature increase,
 approx. 1.5 2 °C/min
- For reliable function and long life-time
- Guaranteed reproducible quality
 For optimum products
- Reliable batch tracking
 Allows for trouble-free quality
 management


Low material pressureNo caking or material build-ups

production conditions.

- High flexibility
 Quick set-up and change-over
- Intelligent machine frame design No edges, deadspots and obstacles for fast and easy cleaning of the surroundings
- Safe operation
 ATEX-certified with EU- typeexamination certificate (option)







Presented by

Zeppelin Systems GmbH Mixing Technology Henschelplatz 1 34127 Kassel GERMANY Tel.: +49 7541 202 4100 mixingtechnology@zeppelin.com

For the complete Zeppelin Systems range please visit our website at www.zeppelin-systems.com

Global presence

- Australia
- Belgium
- Brazil
- China
- France
- Germany
- India
- Italy
- Korea
- Russia
- Saudi Arabia
- Singapore
- United Kingdom
- USA

^{*} Mixing tool patent: EP 3 342 480 B1